COYERALL AUTOCLAVE

MULTI-USE AUTOCLAVABLE

COVERALL AUTOCLAVE protective goggles is specially designed to guarantee total comfort and optimum protection in controlled environments. Equipped with our exclusive anti-fog and anti-scratch PLATINUM coating on both sides of the lens, our autoclavable multi-use goggles are resistant to high temperature and still fully functional after several autoclaving cycles. Its designs fit over any prescription glasses, ensuring improved eye protection and vision.

- 4 AUTOCLAVE COMPATIBLE PRODUCT
- + LIQUID OVERFLOW CHUTE
- TANTI-FOG AND ANTI-SCRATCH PLATINUM COATING



TECHNOLOGIES

*PLATINUM

VERSIONS



COVACLAVE



COVACLEAN



COVERALL CLEAN

NON-STERILE SINGLE-USE

COVERALL CLEAN protective goggles is specially designed to guarantee total comfort and optimum protection in sensitive and sterile environments such as pharmacies, micro-electronics and operating theatres. Disposable non-sterile goggles that can be treated by the customer by gamma or beta irradiation or by ethylene oxide sterilisation.

- TO CAN BE STERILIZED USING GAMMA, BETA AND ETO RADIATION
- DISPOSABLE
- → ANTI-SCRATCH/ANTI-FOG
 PLATINUM LITE COATING



TECHNOLOGIES

*PLATINUM LITE

VERSIONS



COVACLAVE



COVACLEAN



COVERALL								
USE	VERSION	REFERENCE	LENS MARKING	FRAME MARKING	COATING	STANDARD		
\otimes	CLEAR	COVACLAVE	≌ Z87+ U6	≅ Z87+ D3 D4	⊅L∕TINUM	ANSI Z87.1-2010		
	CLEAR	COVACLEAN	' Z87+ U6	≌ Z87+ D3 D4	† PLATINUM LITE	ANSI Z87.1-2010		

WARNING: Can expose you to Bisphenol-A (BPA), a carcinogen and reproductive toxicant. See www.P65Warnings.ca.gov.

COVACLAVE: GENERAL SPECIFICATIONS					
LENS	POLYCARBONATE				
FRAME	TPR - INDIRECT VENTILATED ON THE UPPER PART AND SEALED ON THE BOTTOM				
WEIGHT	2.72 oz				
STRAP	ISOPRENE - GREY				
USE	MULTI USE - AUTOCLAVE				

COVACLEAN: GENERAL SPECIFICATIONS				
LENS	POLYCARBONATE			
FRAME	PVC - INDIRECT VENTILATED ON THE UPPER PART AND INDIRECT VENTILATED ON THE BOTTOM			
WEIGHT	3.32 oz			
STRAP	ISOPRENE - GREY			
USE	SINGLE USE - STERILIZABLE			



COVACLAVE MADE IN: TW



COVACLEAN MADE IN: TW



OR SCAN:



CLEANING & STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the glasses or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.















DATASHEET: 07-15-2022

bolle-safety.com

Europe Headquarters 34 rue de la Soie 69100 Villeurbanne France Tél.: 00 33 (0) 4 78 85 23 64 U.K. & Ireland Unit C83 - Barwell Business Park Leatherhead Road - Chessington Surrey - KT9 2NY - UK Tél. : 00 44 (0)208 391 4700 USA Office 2810 Caribou Court, Suite 160 Carlsbad, CA 92010 United States of America Tél.: 800 222 6553 Asia-Pacific Office 32-40 Fairchild Street heatherton VIC 3202 Australia Tél.: 1300 138 098

