

KOMET

COST-EFFECTIVE SOLUTION

Thanks to its ultra wrap-around design, thin temple arms and a high clarity polarised lens, KOMET provides the best combination of comfort and effective protection. Also available in smoke and red flash versions.



31g



PSSKOME01 : POLARIZED



PSSKOME408 : Smoke



PSSKOMEF06 : Red Flash









PSPUNISS01 (optional)
Strap

- + ULTRA WRAP-AROUND FRAME**
- + LINEAR DESIGN OF THE TEMPLE ARMS**
- + POLARISED VERSION REDUCES GLARE AND PROVIDES OPTIMUM PROTECTION**
- + NO METAL PARTS**
- + UNISEX DESIGN**

bolle
SAFETY

KOMET

COST-EFFECTIVE SOLUTION

| MODEL | VERSIONS | REFERENCES | LENS MARKING | FRAME MARKING | COATINGS |
|-------|--|------------|--|--------------------|-----------------------|
| KOMET |  POLARIZED | PSSKOME01 |  I3 | AS/NZS 1337.1:2010 | Anti-scratch |
| |  Smoke | PSSKOME408 |  I3 | AS/NZS 1337.1:2010 | Anti-scratch/Anti-fog |
| |  Red Flash | PSSKOMEF06 |  I3 | AS/NZS 1337.1:2010 | Anti-scratch |
| | Strap only (optional) | PSPUNISS01 | - | - | - |

LENS MARKING

- I. The letter 'I' signifies 'Medium Impact' approval.
- O. The letter 'O' signifies that the product has been approved for the use both outdoors and indoors, and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses.

Ocular lens category:

- O. Range of luminous transmittance 80–100%
- 1. Range of luminous transmittance 43–88%
- 3. Range of luminous transmittance 8–18%

Others symbols:

 Manufacturer name

TECHNOLOGIES

POLARIZED

A technology approved for permanent wear and certified with perfect optical quality, it offers unbeatable comfort by filtering glare and reflections. Ideal for the maritime environment. Filters 99.99% of UVA/UVB.

FRAME MARKING

AS/NZS 1337.1:2010 : Tested and approved to AS/NZS 1337.1.2010 for medium impact protection. Resists a 6mm ball at 45 m/s.

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

PACKAGING AND EAN13 CODE

| | PSSKOME01 | PSSKOME408 | PSSKOMEF06 |
|--------------------------------------|---------------|---------------|---------------|
| Individual plastic bag | 3660740013158 | 3660740013165 | 3660740013196 |
| 10 safety spectacles per inner box | 3660740113155 | 3660740113162 | 3660740113193 |
| 240 safety spectacles per outer pack | 3660740213152 | 3660740213169 | 3660740213190 |

CHARACTERISTICS

| | |
|--------------|-----------------------|
| LENSES | PC – 2mm – Curve 8 |
| FRAME | - |
| TEMPLES | PC |
| STRAP | Nylon/15mm/Adjustable |
| SPARE LENSES | No |



08/10/2021

Bollé Safety AU Pty Limited
 32–40 Fairchild Street
 Heatherton VIC 3202
 Customer Service:
 AU: 1300 138 098 NZ: 0800 2655 369
 E: sales@bollesafety.com.au

bollesafety.com.au

bolle
SAFETY